


TECNOLUMEN

TECNOLUMEN GmbH & Co. KG • Lötzeener Str. 2-4 • D-28207 Bremen • Tel (0421) 430 41 70 • Fax (0421) 4986685

Important Information!

Flexible-arm lamp EB 27 & EB 28

After opening the box,
please handle the lamp as shown on the pictures:



Right!



Wrong!

Technical details:

Power supply: 110-240 V / 50-60 Hz

EU: Transformer:

USA: Transformer:

Maximum wattage (thermal):

Supplied bulb:

Bulb socket: GY6.35

Protection class: I

230-240 V / 12 V AC

110 V / 12 V AC

HAL 50 W

Halogen bulb, 12 V, 50 W

Safety instructions:

- Never cover the luminaire with a cloth – fire hazard!
- Always ensure that the plug is removed from the socket before working on the luminaire or changing the bulb.
- Have repair work performed only by an authorized electrician, because electrical power can cause severe injuries!
- Some of the lamp components may get very hot in operation! Avoid skin contact with these components to prevent burns.

Care of lamp:

EB27/28 silver / nickel: In the course of time a silver-colored patina forms on the nickel plated brass parts, which is frequently desired. If you want him surface to retain a glossy nickel-plated finish for reasons of appearance, use for the silver lamp the enclosed silver gloves or a silver polish and for the nickel one a chrome polish. Apply the polish only with a cotton wool and beware circularly movements, because silver and nickel are pettishly surfaces, they are easy to scratch.

EB27/28 Chrome: Chromed surfaces are harder and much impassibly. You can use a chrome polish.